

## Pinching Force Measurement Jig PCA-150N

- Pinching and opening (spreading) action-force measurement jig for small size objects.
- Designed to measure a variety of industrial, medical, and daily use products such as: -Pinch and Double handle tools - Forceps, Nippers, Pliers, Clamps, Pincer and Tongs.
- The scale attached helps easy measuring widths adjustment.
- Measurement with simple steps of only mounting a force gauge, and lightweight to carry.





Applicable Samples

Forceps, Tongs, Clamps, Pliers, Pincers, Nippers, Vernier-calipers, Chopsticks, etc.

How used Example				
Screw onto the	Mount Force Gauge to	Adjust the pinching width	Pinch to apply force from	
Measuring Shaft	the jig base	with the scale	both sides	



Specification		
Model	PCA-150N	
Capacity	150N	
Max. Pinching widths of the Sample	43mm	
Max. Pinching widths	5∼15mm	
Max. Spreading section widths of the jig	1∼15mm	
Dimensions	Refer to the diagram	
Total weight / (Upper jig weight) *1	Approx. 360g / (Approx. 50g)	

<sup>\*1</sup> Weight of the attachment is also applied as a load on the force gauge. Consider it when selecting the capacity of a force gauge.

Examples: Product configuration		
Example 1 Code: 1P2012A	d	
Basic Operation Measurement up to 150N		
Digital force gauge: DST-200N Optional attachment: PCA-150N		
Example 2 Code: 1P2012B		
With an internal data management function. Measurement up to 150N		
Digital force gauge ZTS-200N Optional attachment: PCA-150N	Example 2 Image	

- \* Refer to the specification of each product for details.
- \* Product configuration varies depending on the shape and characteristic of the sample, and measurement conditions.
- \* The recommended capacity of force gauge varies depending on the expected force to be loaded.

Compatible Force gauges		
DST/DSV Series with capacity 50N or over *1 (Digital Force-Gauge)	ZTS/ZTA Series with capacity 50N or over *1 (Digital Force-Gauge)	
Cost-effective with data management facility with PC	Various internal functions with high responsiveness support accurate measurements	

<sup>\*1</sup> Recommended range that weight of the attachment is also applied as a load on the force gauge.


Related Products		
Acupuncture Needle: Strength and Sharpness Test  MED-ACU-2N	Load cell: Two-wheeler Vehicles' Handbrake Tests <b>PK1-500N</b>	
Designed to measure the strength and sharpness	A dedicated load cell for measuring	
of the Acupuncture needle.	Handgrip brake force of the two-wheeler vehicle.	



Possible range of custom made		
Max Sample Widths**	To be confirmed upon inquiry	
Min. Pinching Widths	2mm	
Max. Capacity**	To be confirmed upon inquiry	

<sup>\*\*</sup> For us to confirm accurate details and options, please provide details of your requirements in advance.

## [Dimensions]



## [Caution]

- Information in this document is subject to change without prior notice.
- This document is product descriptions and handling precautions, and do not guarantee various characteristics or safety.
- This product designed for force measurement purposes only.
- Do not copy and use this content without authorization.
- A force gauge (sold separately) is required to use this product.
- Some samples may not be suitable to measure with this product.

SHRADDHA IMPEX Authorized Distributor

Email: shraddhaimpex@gmail.com / sales@shraddhaimpex.net

Web: www.shraddhaimpex.net

Contact: +919819530352 / +918591279918

